





Dekkramme Gira E2 med tekstfelt renhvit silkematt



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---|-----------------|-----|----|---------------|
|  Enkel | 1091 22 | 10 | 01 | 4010337084037 |
|  Dobbel horisontal | 1092 22 | 10 | 01 | 4010337084082 |
|  Dobbel lodrett | 1102 22 | 10 | 01 | 4010337089131 |
|  3-dobbel horisontal | 1093 22 | 1/5 | 01 | 4010337084167 |
|  3-dobbel vertikal | 1103 22 | 1/5 | 01 | 4010337084204 |
|  4-dobbel horisontal | 1094 22 | 1/5 | 01 | 4010337084242 |
|  4-dobbel loddrett | 1114 22 | 1 | 01 | 4010337084280 |
|  5-dobbel horisontal | 1095 22 | 1/5 | 01 | 4010337084365 |
|  5-dobbel loddrett | 1115 22 | 1/5 | 01 | 4010337084327 |

Egenskaper

- Bruddsikker.
 - Sprøytetåketett.
 - Dekkramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-