










Høytaler innfelt RDS-radio



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvít glanset	2282 01	1	03	4010337076230
 renhvít glanset	2282 03 6306546	1	03	4010337076247
 antrasitt	2282 28	1	03	4010337076261
 aluminiumsfarget	2282 26	1	03	4010337076162
 svart glass-finish	2282 05	1	03	4010337889182
 svart matt	2282 005	1	03	4010337037286
 grå matt	2282 015	1	03	4010337083931
 edelstål	2282 600	1	03	4010337032861

Egenskaper

- Høytaler for tilkobling til Gira innfelt RDS-radio.

Tekniske data

Monteringsdybde:	32 mm
Tilkoblingstverrsnitt - Høytaler-/AUX-tilkobling:	1,5 mm ²
Omgivelsestemperatur:	-5 °C til +50 °C
