








Barbermaskinkontakt (DIN EN 61558 2-5) 115–230 V~ for dekkramme, dobbel uten mellomstykke



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvitt glans	2820 01	1	29	4010337016755
 renhvitt glans	2820 03	1	29	4010337016762
 antrasitt	2820 28	1	29	4010337016809
 aluminiumsfarget	2820 26	1	29	4010337016793
 svart matt	2820 005	1	29	4010337037323
 grå matt	2820 015	1	29	4010337087090
 rustfritt stål (lakkert)	2820 600	1	29	4010337021995