








Vippebryter British Standard (BS EN 60669-1) 3-kanals med vipper Universal-utkoblingsvendebryter



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	2832 01	10	29	4010337832010
 renhvit glans	2832 03	10	29	4010337832034
 antrasitt	2832 28	10	29	4010337832287
 aluminiumsfarget	2832 26	10	29	4010337832263
 svart matt	2832 005	10	11	4010337038528
 grå matt	2832 015	10	11	4010337087120
 rustfritt stål (lakkert)	2832 600	10	29	4010337022053

Egenskaper

- Med skruklemmer.

Tekniske data

Monteringsdybde: 25 mm

Tilkoblingstverrsnitt
- For ledninger inntil: 2,5 mm²

Merknader

- Kun for skruefeste.
