








**Vippebryter British Standard (BS EN 60669-1) 20 AX 250 V~med vippe og kontrolllys
Utkoblingsbryter 2-polet**

Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	2834 01	10	29	4010337078814
 renhvit glans	2834 03	10	29	4010337078821
 antrasitt	2834 28	10	29	4010337078845
 aluminiumsfarget	2834 26	10	29	4010337078838
 svart matt	2834 005	10	29	4010337038573
 grå matt	2834 015	10	29	4010337087137
 rustfritt stål	2834 600	10	29	4010337022305

Egenskaper

- Med skruklemmer.

Tekniske data

Monteringsdybde:	24 mm
Tilkoblingstverrsnitt - For ledninger inntil:	2 x 4 mm ² eller 1 x 6 mm ²

Merknader

- Kun for skruefeste.
 - BS EN 60669-1.
-