








Vippetrykkbryter 3-dobbel 10 A 250 V~med vipper Lukkekontakt 1-polet



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	2844 01	10	29	4010337082033
 renhvit glans	2844 03	10	29	4010337082040
 antrasitt	2844 28	10	29	4010337082064
 aluminiumsfarget	2844 26	10	29	4010337082057
 svart matt	2844 005	10	29	4010337037903
 grå matt	2844 015	10	29	4010337087182
 rustfritt stål (lakkert)	2844 600	10	29	4010337021957

Egenskaper

- Med skruklemmer.

Tekniske data

Monteringsdybde: 25 mm

Tilkoblingstverrsnitt
- For ledninger inntil: 2,5 mm²

Merknader

- Kun for skruefeste.
