









## Vippe med kontrollvindu



| Spesifikasjon   | Bestillings nr. | PE     | PS | EAN           |
|---|-----------------|--------|----|---------------|
|  kremhvit glans      | 3290 01         | 1      | 01 | 4010337041610 |
|  renhvit glans     | 3290 03         | 10/100 | 01 | 4010337041627 |
|  renhvit silkematt | 3290 27         | 10     | 01 | 4010337041641 |
|  antrasitt         | 3290 28         | 10     | 11 | 4010337041658 |
|  aluminiumsfarget  | 3290 26         | 1      | 11 | 4010337041634 |
|  svart matt        | 3290 005        | 10     | 11 | 4010337067047 |
|  grå matt          | 3290 015        | 10     | 11 | 4010337110491 |
|  rustfritt stål    | 3290 600        | 1/5    | 11 | 4010337045403 |