









## Vippe



| Spesifikasjon   | Bestillings nr. | PE     | PS | EAN           |
|---|-----------------|--------|----|---------------|
|  kremhvit glans      | 3296 01         | 10     | 21 | 4010337039341 |
|  renhvit glans     | 3296 03         | 10/100 | 21 | 4010337039358 |
|  renhvit silkematt | 3296 27         | 10/100 | 21 | 4010337039372 |
|  antrasitt         | 3296 28         | 10/100 | 11 | 4010337039389 |
|  aluminiumsfarget  | 3296 26         | 10     | 11 | 4010337039365 |
|  svart matt        | 3296 005        | 10     | 11 | 4010337065593 |
|  grå matt          | 3296 015        | 10     | 11 | 4010337110521 |
|  rustfritt stål    | 3296 600        | 10     | 11 | 4010337043867 |