








## System 3000 betjeningsmodul, dobbel



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	5362 01	1/5	02	4010337063841
 renhvit glans	5362 03	1/5	02	4010337063858
 antrasitt	5362 28	1/5	02	4010337063902
 aluminiumsfarget	5362 26	1	02	4010337063889
 svart matt	5362 005	1/5	02	4010337063919
 grå matt	5362 015	1/5	02	4010337087229
 rustfritt stål	5362 600	1	02	4010337063926

### Tekniske data

Omgivelsestemperatur: -20 °C til +45 °C