









**Bæring Modular Jack dobbel**  
**Bæring MJ-01 til MJ-10**

Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Bæring MJ-01	5601 00 6944031	10	01	4010337460015
 Bæring MJ-02	5602 00 6944032	10	01	4010337460022
 Bæring MJ-03	5603 00	10	01	4010337460039
 Bæring MJ-04	5604 00 6944034	10	01	4010337460046
 Bæring MJ-05	5605 00 6944035	10	01	4010337460053
 Bæring MJ-06	5606 00 6944036	10	01	4010337460060
 Bæring MJ-07	5607 00 6944037	10	01	4010337460077
 Bæring MJ-08	5608 00 6944038	10	01	4010337460084
 Bæring MJ-09	5609 00 6944039	10	01	4010337460091



Bæring MJ-10

5610 00  
6944040

10

01

4010337460107

---

## Merknader

- Kun for skruefeste.
  - Egnert for kanalinstallasjon.
- 

## Mål i mm

MJ-01, MJ02, MJ-07:	B 14,8	H 19,5
MJ-03:	B 14,8	H 20,0
MJ-04, MJ-09:	B 14,8	H 19,3
MJ-05:	B 16,7	H 17,3
MJ-06:	B 15,9	H 18,3
MJ-08:	B 14,8	H 19,0
MJ-10:	B 16,1	H 18,5

---