


Ramka Gira E2 antracytowy



| Specyfikacja | Nr katalogowy | Jednostka opakowania | SC | EAN |
|---|---------------|----------------------|----|---------------|
|  1x | 0211 23 | 10/100 | 11 | 4010337211235 |
|  1,5x | 1001 23 | 10 | 11 | 4010337881339 |
|  2x | 0212 23 | 10/100 | 11 | 4010337212232 |
|  2x, bez przegrody | 1002 23 | 10 | 11 | 4010337002239 |
|  3x | 0213 23 | 1/5 | 11 | 4010337213239 |
|  4x | 0214 23 | 1/5 | 11 | 4010337214236 |
|  5x | 0215 23 | 1/5 | 11 | 4010337215233 |

Wskazówki

- Przystosowane również do instalacji w kanałach.
- Ramka (1x do 5x) w połączeniu z zestawem uszczelnień nadają się również do instalacji bryzgoszczelnej podtynkowej IP44.