

Ramka Gira E3
powierzchnia szara typu Soft Touch z ramką nośną w kolorze antracytu



| Specyfikacja | Nr katalogowy | Jednostka opakowania | SC | EAN |
|---|---------------|----------------------|----|---------------|
|  1x | 0211 422 | 10 | 11 | 4010337023951 |
|  2x | 0212 422 | 10 | 11 | 4010337023968 |
|  2x, bez przegrody | 1002 422 | 10 | 11 | 4010337024019 |
|  3x | 0213 422 | 1/5 | 11 | 4010337023975 |
|  4x | 0214 422 | 1/5 | 11 | 4010337023982 |
|  5x | 0215 422 | 1/5 | 11 | 4010337023999 |

Właściwości

- Udaroodporne.

Wskazówki

- Powierzchnia typu Soft Touch.
- Wartość NCS: bliska NCS S 3500-N