












## Ośłona z zaślepką nasadzaną do moduł nakładany czujnika ruchu nego 1,10 m Standard



Specyfikacja	Nr katalogowy	Jednostka opakowania	SC	EAN
 kremowy z połyskiem	1470 01	1	02	4010337020967
 czysta biel z połyskiem	1470 03	1	02	4010337020974
 kolor aluminium	1470 26	1	02	4010337030010
 czysta biel, matowy	1470 27	1	02	4010337075257
 antracytowy	1470 28	1	02	4010337075264
 szary	1470 42	1	02	4010337075295
 kolor aluminium	1470 65	1	02	4010337075516
 czysta biel	1470 66	1	02	4010337075523
 antracytowy	1470 67	1	02	4010337075530

	czysta biel z połyskiem	1470 112	1	02	4010337075240
	czysta biel	1470 40	1	02	4010337075271