

Gniazdo do golarki (DIN EN 61558 2-5) 115 - 230 V~ do ramki 2x bez przegrody



| Specyfikacja | Nr katalogowy | Jednostka opakowania | SC | EAN |
|---|---------------|----------------------|----|---------------|
|  kremowy z połyskiem | 2820 01 | 1 | 29 | 4010337016755 |
|  czysta biel z połyskiem | 2820 03 | 1 | 29 | 4010337016762 |
|  antracytowy | 2820 28 | 1 | 29 | 4010337016809 |
|  kolor aluminium | 2820 26 | 1 | 29 | 4010337016793 |
|  czarny matowy | 2820 005 | 1 | 29 | 4010337037323 |
|  szary matowy | 2820 015 | 1 | 29 | 4010337087090 |
|  stal szlachetna (lakierowana) | 2820 600 | 1 | 29 | 4010337021995 |