

Łącznik kołyskowy British Standard (BS EN 60669-1) 3x z klawiszami
Łącznik uniwersalny



| Specyfikacja | Nr katalogowy | Jednostka opakowania | SC | EAN |
|---|---------------|----------------------|----|---------------|
|  kremowy z polyskiem | 2832 01 | 10 | 29 | 4010337832010 |
|  czysta biel z polyskiem | 2832 03 | 10 | 29 | 4010337832034 |
|  antracytowy | 2832 28 | 10 | 29 | 4010337832287 |
|  kolor aluminium | 2832 26 | 10 | 29 | 4010337832263 |
|  czarny matowy | 2832 005 | 10 | 11 | 4010337038528 |
|  szary matowy | 2832 015 | 10 | 11 | 4010337087120 |
|  stal szlachetna (lakierowana) | 2832 600 | 10 | 29 | 4010337022053 |

Właściwości

- Z zaciskami śrubowymi.

Dane techniczne

Głębokość montażu: 25 mm

Przekrój przyłącza
- do przewodów do: 2,5 mm²

Wskazówki

- Tylko do mocowania śrubowego.
