









Gniazdo wtyczkowe SCHUKO 16 A 250 V~z polem opisowym System 55



Specyfikacja	Nr katalogowy	Jednostka opakowania	SC	EAN
 kremowy z połyskiem	4457 01	1/5	01	4010337093244
 czysta biel z połyskiem	4457 03	1/5	01	4010337093268
 czysta biel, matowy	4457 27	1/5	01	4010337093329
 antracytowy	4457 28	1/5	11	4010337093336
 kolor aluminium	4457 26	1/5	11	4010337093312
 czarny matowy	4457 005	1/5	11	4010337093237
 szary matowy	4457 015	1/5	11	4010337093251
 stal szlachetna (lakierowana)	4457 600	1/5	11	4010337093343

Dane techniczne

Głębokość montażu:	31 mm
Przekrój przyłącza - do przewodów:	od 1,5 mm ² do 2,5 mm ²

Ilustracje i tym podobne mogą odbiegać od oryginałów.

Zakres dostawy

- Tabliczka opisowa „EDV” jest dołączona.
