










**Pierścień nośny Modular Jack 2x**  
**Element montażowy MJ-01 do MJ-10**



Specyfikacja	Nr katalogowy	Jednostka opakowania	SC	EAN
 Pierścień nośny MJ-01	5601 00	10	01	4010337460015
 Pierścień nośny MJ-02	5602 00	10	01	4010337460022
 Pierścień nośny MJ-03	5603 00	10	01	4010337460039
 Pierścień nośny MJ-04	5604 00	10	01	4010337460046
 Pierścień nośny MJ-05	5605 00	10	01	4010337460053
 Pierścień nośny MJ-06	5606 00	10	01	4010337460060
 Pierścień nośny MJ-07	5607 00	10	01	4010337460077
 Pierścień nośny MJ-08	5608 00	10	01	4010337460084
 Pierścień nośny MJ-09	5609 00	10	01	4010337460091



Pierścień nośny MJ-10

5610 00

10

01

4010337460107

## Wskazówki

- Tylko do mocowania śrubowego.
- Nadaje się do instalacji kanałowej.

## Wymiary w mm

MJ-01, MJ02, MJ-07:	S 14,8	H 19,5
MJ-03:	S 14,8	H 20,0
MJ-04, MJ-09:	S 14,8	H 19,3
MJ-05:	S 16,7	H 17,3
MJ-06:	S 15,9	H 18,3
MJ-08:	S 14,8	H 19,0
MJ-10:	S 16,1	H 18,5