










**Pierścień nośny Modular Jack 2x**  
**Element montażowy MJ-01 do MJ-10**



| Specyfikacja  | Nr katalogowy | Jednostka opakowania | SC | EAN           |
|---|---------------|----------------------|----|---------------|
|  Pierścień nośny MJ-01  | 5601 00       | 10                   | 01 | 4010337460015 |
|  Pierścień nośny MJ-02 | 5602 00       | 10                   | 01 | 4010337460022 |
|  Pierścień nośny MJ-03 | 5603 00       | 10                   | 01 | 4010337460039 |
|  Pierścień nośny MJ-04 | 5604 00       | 10                   | 01 | 4010337460046 |
|  Pierścień nośny MJ-05 | 5605 00       | 10                   | 01 | 4010337460053 |
|  Pierścień nośny MJ-06 | 5606 00       | 10                   | 01 | 4010337460060 |
|  Pierścień nośny MJ-07 | 5607 00       | 10                   | 01 | 4010337460077 |
|  Pierścień nośny MJ-08 | 5608 00       | 10                   | 01 | 4010337460084 |
|  Pierścień nośny MJ-09 | 5609 00       | 10                   | 01 | 4010337460091 |



Pierścień nośny MJ-10

5610 00

10

01

4010337460107

## Wskazówki

- Tylko do mocowania śrubowego.
- Nadaje się do instalacji kanałowej.

## Wymiary w mm

|                     |        |        |
|---------------------|--------|--------|
| MJ-01, MJ02, MJ-07: | S 14,8 | H 19,5 |
| MJ-03:              | S 14,8 | H 20,0 |
| MJ-04, MJ-09:       | S 14,8 | H 19,3 |
| MJ-05:              | S 16,7 | H 17,3 |
| MJ-06:              | S 15,9 | H 18,3 |
| MJ-08:              | S 14,8 | H 19,0 |
| MJ-10:              | S 16,1 | H 18,5 |