


Vippbrytare 10 AX 250 V~med vippa Universal-av-trapp



Specifikation	Artikelnr.	FE	PS	EAN
 kritvit blank	0106 03 1851421	1/5	01	4010337106036
 kritvit sidenmatt	0106 27 1851221	1/5	01	4010337106272
 antracit	0106 28 1851321	1/5	11	4010337106289
 alufärg	0106 26 1851021	1	11	4010337106265
svart matt	0106 005 1850388	1	11	4010337038559
 rostfritt stål	0106 600 1850345	1	11	4010337028406

Tekniska data

Inbyggnadsdjup:	28 mm
Anslutningsarea - För styva och flexibla ledare upp till:	2,5 mm²
Nominell effekt - LEDi/ CFLi:	100 W

Hänvisningar

- Kan även anslutas med belysning.
