








Knappbrytare 10 AX 250 V~med rakt stående vippra Universal-av-trapp



Specifikation	Artikelnr.	FE	PS	EAN
 kritvit blank	0121 201 1853121	1/5	01	4010337052692
 kritvit sidenmatt	0121 27	1/5	01	4010337029311
 antracit	0121 28	1/5	11	4010337029335
 alufärg	0121 26	1	11	4010337029328
 svart matt	0121 005 1850392	1	11	4010337037972
 grå matt	0121 015 1850411	1	11	4010337077091
 rostfritt stål	0121 600 1850350	1/5	11	4010337021261

Tekniska data

Inbyggnadsdjup:	28 mm
Anslutningsarea - För styva och flexibla ledare upp till:	2,5 mm ²
Nominell effekt - LEDi/ CFLi:	100 W

Hänvisningar

- Beroende på tillgänglighet.
