








## Knappbrytare 10 AX 250 V~med rakt stående vippra Universal-av-trapp



| Specifikation   | Artikelnr.          | FE  | PS | EAN           |
|---|---------------------|-----|----|---------------|
|  kritvit blank      | 0121 201<br>1853121 | 1/5 | 01 | 4010337052692 |
|  kritvit sidenmatt | 0121 27             | 1/5 | 01 | 4010337029311 |
|  antracit          | 0121 28             | 1/5 | 11 | 4010337029335 |
|  alufärg           | 0121 26             | 1   | 11 | 4010337029328 |
|  svart matt        | 0121 005<br>1850392 | 1   | 11 | 4010337037972 |
|  grå matt          | 0121 015<br>1850411 | 1   | 11 | 4010337077091 |
|  rostfritt stål    | 0121 600<br>1850350 | 1/5 | 11 | 4010337021261 |

### Tekniska data

|  |                     |
|--|---------------------|
| Inbyggnadsdjup:  | 28 mm               |
| Anslutningsarea<br>- För styva och flexibla ledare upp till: | 2,5 mm <sup>2</sup> |
| Nominell effekt<br>- LEDi/ CFLi:                             | 100 W               |

---

## Hänvisningar

- Beroende på tillgänglighet.

---