








Knappbrytare 10 AX 250 V~med rakt stående vippa Kryssbrytare



Specifikation	Artikelnr.	FE	PS	EAN
 kritvit blank	0123 201 1850631	1/5	01	4010337052708
 kritvit sidenmatt	0123 27	1/5	01	4010337029342
 antracit	0123 28	1/5	11	4010337029366
 alufärg	0123 26	1	11	4010337029359
 svart matt	0123 005	1	11	4010337037996
 grå matt	0123 015	1	11	4010337077114
 rostfritt stål	0123 600	1	11	4010337021254

Tekniska data

Inbyggnadsdjup:	28 mm
Anslutningsarea - För styva och flexibla ledare upp till:	2,5 mm ²
Nominell effekt - LEDi/ CFLi:	100 W

Hänvisningar

- Beroende på tillgänglighet.
