

## Tryck-kontrollbrytare 10 AX 250 V~med rakt stående vippra Universal-av-trapp



Specifikation	Artikelnr.	FE	PS	EAN
 kritvit blank	0124 201 1853162	1/5	01	4010337052715
 kritvit sidenmatt	0124 27	1/5	01	4010337029403
 antracit	0124 28	1/5	11	4010337029427
 alufärg	0124 26	1	11	4010337029410
 svart matt	0124 005	1	11	4010337037958
 rostfritt stål	0124 600 1850351	1	11	4010337021230

### Tekniska data

Inbyggnadsdjup:	28 mm
Anslutningsarea - För styva och flexibla ledare upp till:	2,5 mm <sup>2</sup>
Nominell effekt - LEDi/ CFLi:	100 W

## Hänvisningar

- Kan även anslutas med belysning.
  - Beroende på tillgänglighet.
- 

## Leveransen innehåller

- Glimlampselement 230 V~, 1,5 mA ingår i leveransen.
-