









Knappbrytare 10 AX 250 V~ med vippta 2-knappars Kronbrytare



Specifikation	Artikelnr.	FE	PS	EAN
 cremevit blank	0125 01	1/5	01	4010337125013
 kritvit blank	0125 03 1851716	1/5	01	4010337125037
 kritvit sidenmatt	0125 27	1/5	01	4010337125273
 antracit	0125 28	1/5	11	4010337125280
 alufärg	0125 26	1/5	11	4010337125266
 svart matt	0125 005	1/5	11	4010337038016
 grå matt	0125 015	1/5	11	4010337077138
 rostfritt stål	0125 600	1/5	11	4010337021780

Tekniska data

Inbyggnadsdjup
- 0125 ...:

28 mm

- 0128 ...:	32 mm
Anslutningsarea	
- För styva och flexibla ledare upp till:	2,5 mm ²
Nominell effekt	
- LEDi/ CFLi:	100 W

Hänvisningar

- Beroende på tillgänglighet.
