










Knappbrytare 10 AX 250 V~ med vippta Universal-av-trapp



Specifikation	Artikelnr.	FE	PS	EAN
 cremevit blank	0126 01	1/5	01	4010337126010
 kritvit blank	0126 03 1851721	1/5	01	4010337126034
 kritvit sidenmatt	0126 27	1/5	01	4010337126270
 antracit	0126 28	1/5	11	4010337126287
 alufärg	0126 26	1/5	11	4010337126263
 svart matt	0126 005	1/5	11	4010337037965
 grå matt	0126 015	1/5	11	4010337077145
 rostfritt stål	0126 600	1/5	11	4010337021742

Tekniska data

Inbyggnadsdjup: 28 mm

Anslutningsarea
- För styva och flexibla ledare upp till: 2,5 mm²

Bilder är liknande och kan avvika från originalet.

Nominell effekt

- LEDi/ CFLi:

100 W

Hänvisningar

- Beroende på tillgänglighet.
