

Knappbrytare 10 AX 250 V~ med vippra Kryssbrytare



Specifikation	Artikelnr.	FE	PS	EAN
 cremevit blank	0127 01	1/5	01	4010337127017
 kritvit blank	0127 03 1851731	1/5	01	4010337127031
 kritvit sidenmatt	0127 27	1/5	01	4010337127277
 antracit	0127 28	1/5	11	4010337127284
 alufärg	0127 26	1/5	11	4010337127260
 svart matt	0127 005	1/5	11	4010337037989
 grå matt	0127 015	1/5	11	4010337077169
 rostfritt stål	0127 600	1/5	11	4010337021759
 brons	0127 603	1/5	11	4010337106067

Tekniska data

Inbyggnadsdjup:	28 mm
Anslutningsarea	
- För styva och flexibla ledare upp till:	2,5 mm ²
Nominell effekt	
- LEDi/ CFLi:	100 W
