

## Knappbrytare 10 AX 250 V~ med vippra Kryssbrytare



| Specifikation                                                                                         | Artikelnr.         | FE  | PS | EAN           |
|-------------------------------------------------------------------------------------------------------|--------------------|-----|----|---------------|
|  cremevit blank     | 0127 01            | 1/5 | 01 | 4010337127017 |
|  kritvit blank     | 0127 03<br>1851731 | 1/5 | 01 | 4010337127031 |
|  kritvit sidenmatt | 0127 27            | 1/5 | 01 | 4010337127277 |
|  antracit          | 0127 28            | 1/5 | 11 | 4010337127284 |
|  alufärg           | 0127 26            | 1/5 | 11 | 4010337127260 |
|  svart matt        | 0127 005           | 1/5 | 11 | 4010337037989 |
|  grå matt          | 0127 015           | 1/5 | 11 | 4010337077169 |
|  rostfritt stål    | 0127 600           | 1/5 | 11 | 4010337021759 |
|  brons             | 0127 603           | 1/5 | 11 | 4010337106067 |

## Tekniska data

|                                           |                     |
|-------------------------------------------|---------------------|
| Inbyggnadsdjup:                           | 28 mm               |
| Anslutningsarea                           |                     |
| - För styva och flexibla ledare upp till: | 2,5 mm <sup>2</sup> |
| Nominell effekt                           |                     |
| - LEDi/ CFLi:                             | 100 W               |

---