









## Knappbrytare 10 AX 250 V~ med vippta 2-knappars Trapp 2knappars



Specifikation	Artikelnr.	FE	PS	EAN
 cremevit blank	0128 01	1/5	01	4010337128014
 kritvit blank	0128 03 1851726	1/5	01	4010337128038
 kritvit sidenmatt	0128 27	1/5	01	4010337128274
 antracit	0128 28	1/5	11	4010337128281
 alufärg	0128 26	1/5	11	4010337128267
 svart matt	0128 005	1/5	11	4010337038030
 grå matt	0128 015	1/5	11	4010337077176
 rostfritt stål	0128 600	1/5	11	4010337021797

### Tekniska data

Inbyggnadsdjup  
- 0125 ...:

28 mm

- 0128 ...:	32 mm
Anslutningsarea - För styva och flexibla ledare upp till:	2,5 mm <sup>2</sup>
Nominell effekt - LEDi/ CFLi:	100 W

---

## Hänvisningar

- Beroende på tillgänglighet.

---