







Vippröckknapp 10 A 250 V~med vippra Slutande kontakt 1-polig



Specifikation	Artikelnr.	FE	PS	EAN
 kritvit blank	0151 03 1851401	1	01	4010337040729
 kritvit sidenmatt	0151 27 1851201	1	01	4010337040743
 antracit	0151 28 1851301	1	11	4010337040750
 alufärg	0151 26 1851001	1	11	4010337040736
svart matt	0151 005	1	11	4010337038627
 rostfritt stål	0151 600 1850355	1	11	4010337028444

Tekniska data

Inbyggnadsdjup: 28 mm

Anslutningsarea
- För styva och flexibla ledare upp till: 2,5 mm²