








Täckram Gira E2 kritvit sidenmatt



| Specifikation | Artikelnr. | FE | PS | EAN |
|---|--------------------|--------|----|---------------|
|  1knapp | 0211 22 1852007 | 10/100 | 01 | 4010337211228 |
|  1,5knappars | 1001 22 1850130 | 10 | 01 | 4010337881322 |
|  2knappars | 0212 22 1852011 | 10/100 | 01 | 4010337212225 |
|  2fack utan mellanbalk | 1002 22 1852009 | 10 | 01 | 4010337002222 |
|  3-knappars | 0213 22 1852015 | 1/5 | 01 | 4010337213222 |
|  4knappars | 0214 22 1852019 | 1/5 | 01 | 4010337214229 |
|  5knappars | 0215 22 1852023 | 1/5 | 01 | 4010337215226 |

Hänvisningar

- Även avsedd för kanalinstallation.
- Täckram (1- till 5-kanals) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.