








## Täckram Gira E2 svart matt



| Specifikation   | Artikelnr.         | FE  | PS | EAN           |
|---|--------------------|-----|----|---------------|
|  1knapp                 | 0211 09<br>1860369 | 10  | 11 | 4010337036739 |
|  1,5knappars           | 1001 09            | 10  | 11 | 4010337072775 |
|  2knappars             | 0212 09<br>1850374 | 10  | 11 | 4010337036760 |
|  2fack utan mellanbalk | 1002 09<br>1850406 | 10  | 11 | 4010337036784 |
|  3-knappars            | 0213 09<br>1850378 | 1/5 | 11 | 4010337036821 |
|  4knappars             | 0214 09<br>1850383 | 1/5 | 11 | 4010337036869 |
|  5knappars             | 0215 09<br>1850385 | 1   | 11 | 4010337036906 |

### Hänvisningar

- Även avsedd för kanalinstallation.
- Täckram (1- till 5-kanals) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.