








## Täckram Gira E2 alufärg



| Specifikation   | Artikelnr.         | FE     | PS | EAN           |
|---|--------------------|--------|----|---------------|
|  1knapp                 | 0211 25<br>1852006 | 10/100 | 11 | 4010337211259 |
|  1,5knappars           | 1001 25<br>1850129 | 10     | 11 | 4010337881346 |
|  2knappars             | 0212 25<br>1852010 | 10     | 11 | 4010337212256 |
|  2fack utan mellanbalk | 1002 25<br>1852017 | 10     | 11 | 4010337002253 |
|  3-knappars            | 0213 25<br>1852014 | 1/5    | 11 | 4010337213253 |
|  4knappars             | 0214 25<br>1852018 | 1/5    | 11 | 4010337214250 |
|  5knappars             | 0215 25<br>1852022 | 1/5    | 11 | 4010337215257 |

### Hänvisningar

- Även avsedd för kanalinstallation.
- Täckram (1- till 5-kanals) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.