








## Täckram Gira Standard 55 cremevit blank



Specifikation	Artikelnr.	FE	PS	EAN
 1knapp	0211 01	10/100	21	4010337211013
 1,5knappars	1001 01	10	01	4010337881247
 2knappars	0212 01	10/100	21	4010337212010
 2fack utan mellanbalk	1002 01	10	01	4010337002017
 3-knappars	0213 01	10/100	01	4010337213017
 4knappars	0214 01	1/5	01	4010337214014
 5knappars	0215 01	1/5	01	4010337215011

### Egenskaper

- Slagtålig.

## Hänvisningar

- Även avsedd för kanalinstallation.
  - Täckram (1- till 5-kanals) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.
-