








Täckram Gira Standard 55 kritvit blank



| Specifikation | Artikelnr. | FE | PS | EAN |
|---|--------------------|--------|----|---------------|
|  1knapp | 0211 03 1854080 | 10/100 | 21 | 4010337211037 |
|  1,5knappars | 1001 03 1850125 | 10 | 01 | 4010337881308 |
|  2knappars | 0212 03 1854081 | 10/100 | 21 | 4010337212034 |
|  2fack utan mellanbalk | 1002 03 1854085 | 10 | 01 | 4010337001607 |
|  3-knappars | 0213 03 1854082 | 10/100 | 01 | 4010337213031 |
|  4knappars | 0214 03 1854083 | 1/5 | 01 | 4010337214038 |
|  5knappars | 0215 03 1854084 | 1/5 | 01 | 4010337215035 |

Egenskaper

- Slagtålig.

Hänvisningar

- Även avsedd för kanalinstallation.
 - Täckram (1- till 5-kanals) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.
-