









Adapterram med kvadratisk öppning för apparater med täckplatta (50 x 50 mm)



| Specifikation | Artikelnr. | FE | PS | EAN |
|---|------------|------|----|---------------|
|  cremevit blank | 0282 01 | 5/25 | 01 | 4010337282013 |
|  kritvit blank | 0282 03 | 5/25 | 01 | 4010337282037 |
|  kritvit sidenmatt | 0282 27 | 5/25 | 01 | 4010337282273 |
|  antracit | 0282 28 | 5/25 | 11 | 4010337282280 |
|  alufärg | 0282 26 | 5/25 | 11 | 4010337282266 |
|  svart matt | 0282 005 | 5/25 | 11 | 4010337036951 |
|  grå matt | 0282 015 | 5/25 | 11 | 4010337078999 |
|  rostfritt stål (lackerat) | 0282 600 | 5/25 | 11 | 4010337022015 |

Egenskaper

- Med adapterramar och täckramar (1- till 5-faldig) kan externa apparater med kvadratisk centralplatta (50 x 50 mm) t. ex. från firmorna Alcatel, AMP Econo Link System, Brand-Rex, BTR, Cellpack ITT Cannon Cat.5, Deutsche Telekom, Drahtex, Hirose, Kannegieter BICC Brand Rex, Kerpen ELine 600, Krone, Molex, Nedap, Panduit, Quante, Reichle de Massari, Rutenbeck, Schumann Netzwerktechnik, HomeWay, Siemens ICCS 100, 300 und 600, Telegärtner, Telenorma, TKM (4 x RJ45) skärmad, Cat.5), etc., integreras i strömbrytarserien.
