









Vippa 2fack



| Specifikation | Artikelnr. | FE | PS | EAN |
|---|---------------------|--------|----|---------------|
|  cremevit blank | 0295 01 | 10 | 01 | 4010337295013 |
|  kritvit blank | 0295 03 1854010 | 10/100 | 01 | 4010337295037 |
|  kritvit sidenmatt | 0295 27 1851825 | 10 | 01 | 4010337295273 |
|  antracit | 0295 28 1851826 | 10 | 11 | 4010337295280 |
|  alufärg | 0295 26 1851824 | 10 | 11 | 4010337295266 |
|  svart matt | 0295 005 1850398 | 10 | 11 | 4010337038078 |
|  grå matt | 0295 015 1850408 | 10 | 11 | 4010337080213 |
|  rostfritt stål | 0295 600 1850391 | 10 | 11 | 4010337021728 |