









Vippa



Specifikation	Artikelnr.	FE	PS	EAN
 cremevit blank	0296 01	10	21	4010337296010
 kritvit blank	0296 03 1854001	10/100	21	4010337296034
 kritvit sidenmatt	0296 27 1851801	10/100	21	4010337296270
 antracit	0296 28 1851802	10/100	11	4010337296287
 alufärg	0296 26 1851800	10	11	4010337296263
 svart matt	0296 005 1850399	10	11	4010337038061
 grå matt	0296 015 1850409	10	11	4010337080220
 rostfritt stål	0296 600 1850393	10	11	4010337021667

Hänvisningar

- Täckram (1- till 5-fack) ur strömställarprogrammet Standard 55 och Gira E2 passar i kombination med tätningssatsen även för kapslad installation, vattenskyddad enligt IP44, av vippbrytare och vipptryckknappar (gäller ej för vippa 2-knappars).

- Beroende på tillgänglighet.
