


Rumstermostat 24/5 (2) A~ med växlande kontakt



Specifikation	Artikelnr.	FE	PS	EAN
 cremevit blank	0397 01	1/5	02	4010337397014
 kritvit blank	0397 03 8580166	1/5	02	4010337397038
 kritvit sidenmatt	0397 27 8580161	1/5	02	4010337397274
 antracit	0397 28 8580162	1/5	02	4010337397281
 alufärg	0397 26 8580160	1/5	02	4010337397267
 svart matt	0397 005 8580517	1/5	02	4010337037446

Tekniska data

Märkspänning:	AC 24 V
Märkström	
- Uppvärmning (öppnande kontakt):	10 (4) A
- Kylning (slutande kontakt):	5 (2) A
Anslutningseffekt	
- Uppvärmning (öppnande kontakt):	ca 240 W
- Kylning (slutande kontakt):	ca 120 W
Bryttemperaturdifferens:	ca 0,5 K
Energiklass:	I = 1 %

Monteringsdjup: 25 mm
Omgivningstemperatur: +5 °C till +30 °C

Hänvisningar

- Endast skruvfastsättning.
 - Kompakt.
-