








Täckram Gira Standard 55 cremevit blank



| Specifikation | Artikelnr. | FE | PS | EAN |
|---|------------|--------|----|---------------|
|  1knapp | 0211 01 | 10/100 | 21 | 4010337211013 |
|  1,5knappars | 1001 01 | 10 | 01 | 4010337881247 |
|  2knappars | 0212 01 | 10/100 | 21 | 4010337212010 |
|  2fack utan mellanbalk | 1002 01 | 10 | 01 | 4010337002017 |
|  3-knappars | 0213 01 | 10/100 | 01 | 4010337213017 |
|  4knappars | 0214 01 | 1/5 | 01 | 4010337214014 |
|  5knappars | 0215 01 | 1/5 | 01 | 4010337215011 |

Egenskaper

- Slagtålig.

Hänvisningar

- Även avsedd för kanalinstallation.
 - Täckram (1- till 5-kanals) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.
-