







## Täckram Gira E2 för platt montering kritvit sidenmatt



| Specifikation   | Artikelnr.          | FE  | PS | EAN           |
|---|---------------------|-----|----|---------------|
|  1knapp                 | 0211 225<br>1850314 | 10  | 01 | 4010337021360 |
|  2knappars             | 0212 225<br>1850322 | 10  | 01 | 4010337021377 |
|  2fack utan mellanbalk | 1002 225            | 10  | 01 | 4010337021407 |
|  3-knappars            | 0213 225<br>1850329 | 1   | 01 | 4010337021384 |
|  4knappars             | 0214 225<br>1850336 | 1/5 | 01 | 4010337021391 |