








Täckram Gira E2 kritvit blank



| Specifikation | Artikelnr. | FE | PS | EAN |
|---|--------------------|--------|----|---------------|
|  1knapp | 0211 29 1852025 | 10/100 | 01 | 4010337211297 |
|  1,5knappars | 1001 29 1850128 | 10 | 01 | 4010337881353 |
|  2knappars | 0212 29 1852026 | 10/100 | 01 | 4010337212294 |
|  2fack utan mellanbalk | 1002 29 1852021 | 10 | 01 | 4010337001553 |
|  3-knappars | 0213 29 1852027 | 1/5 | 01 | 4010337213291 |
|  4knappars | 0214 29 1852028 | 1/5 | 01 | 4010337214298 |
|  5knappars | 0215 29 1852029 | 1/5 | 01 | 4010337215295 |

Hänvisningar

- Även avsedd för kanalinstallation.
- Täckram (1- till 5-kanals) i kombination med tätningssats även lämplig för kapslad infälld IP44 installation.