









Konstantreglage med knappgränssnitt 4-kanals för KNX



Specifikation	Artikelnr.	FE	PS	EAN
 cremevit blank	2100 01	1	06	4010337048022
 kritvit blank	2100 03	1	06	4010337048039
 kritvit sidenmatt	2100 27	1	06	4010337048060
 antracit	2100 28	1	06	4010337048077
 alufärg	2100 26	1	06	4010337048053
 svart matt	2100 005	1	06	4010337037255
 grå matt	2100 015	1	06	4010337083016
 rostfritt stål	2100 600	1	06	4010337021520

Egenskaper

- Temperaturbörvärdet förskjuts med inställningsvredet.
- En närvaroknapp används för omkoppling mellan komfort- och standby-drift.
- De aktuella förhållandena visas på konstantreglaget med LED-lampor.

Tekniska data

Inbyggnadsdjup: 23 mm
