









Vippsats 2-knappars (1+1)



| Specifikation | Artikelnr. | FE | PS | EAN |
|--|------------|----|----|---------------|
|  cremevit blank (lackerad) | 2182 01 | 1 | 06 | 4010337012092 |
|  kritvit blank (lackerad) | 2182 03 | 1 | 06 | 4010337012115 |
|  kritvit sidenmatt (lackerad) | 2182 27 | 1 | 06 | 4010337013372 |
|  antracit (lackerad) | 2182 28 | 1 | 06 | 4010337012139 |
|  alufärg (lackerad) | 2182 26 | 1 | 06 | 4010337012122 |
|  svart matt (lackerad) | 2182 005 | 1 | 06 | 4010337038320 |
|  grå matt (lackerad) | 2182 015 | 1 | 06 | 4010337083160 |
|  rostfritt stål | 2132 601 | 1 | 06 | 4010337020059 |

Hänvisningar

- Vippsatser graverbara och vippsatser utan textfält är gjorda av metall. Detta kan göra att räckvidden begränsas vid radiotillämpningar.