










## Vippsats 3fack



| Specifikation  | Artikelnr. | FE | PS | EAN           |
|--|------------|----|----|---------------|
|  cremevit blank (lackerad)      | 2183 01    | 1  | 06 | 4010337012146 |
|  kritvit blank (lackerad)     | 2183 03    | 1  | 06 | 4010337012153 |
|  kritvit sidenmatt (lackerad) | 2183 27    | 1  | 06 | 4010337013389 |
|  antracit (lackerad)          | 2183 28    | 1  | 06 | 4010337012160 |
|  alufärg (lackerad)           | 2183 26    | 1  | 06 | 4010337012177 |
|  svart matt (lackerad)        | 2183 005   | 1  | 06 | 4010337038382 |
|  grå matt (lackerad)          | 2183 015   | 1  | 06 | 4010337083177 |
|  rostfritt stål               | 2133 601   | 1  | 06 | 4010337020196 |

## Hänvisningar

- Vippsatser graverbara och vippsatser utan textfält är gjorda av metall. Detta kan göra att räckvidden begränsas vid radiotillämpningar.