







Högtalare inbyggd radio



| Specifikation | Artikelnr. | FE | PS | EAN |
|---|--------------------|----|----|---------------|
|  cremevit blank | 2282 01 | 1 | 03 | 4010337076230 |
|  kritvit blank | 2282 03 6240068 | 1 | 03 | 4010337076247 |
|  kritvit sidenmatt | 2282 27 6240070 | 1 | 03 | 4010337076254 |
|  antracit | 2282 28 6240071 | 1 | 03 | 4010337076261 |
|  alufärg | 2282 26 6240069 | 1 | 03 | 4010337076162 |
|  svart glas-design | 2282 05 6240260 | 1 | 03 | 4010337889182 |
|  svart matt | 2282 005 | 1 | 03 | 4010337037286 |
|  grå matt | 2282 015 | 1 | 03 | 4010337083931 |
|  rostfritt stål | 2282 600 | 1 | 03 | 4010337032861 |

Egenskaper

- Högtalare för anslutning till Gira inbyggd radio.

Tekniska data

| | |
|--|---------------------|
| Inbyggnadsdjup: | 32 mm |
| Anslutningsarea - Högtalar-/AUX-anslutning: | 1,5 mm ² |
| impedans: | 8 Ω |
| Omgivningstemperatur: | -5 °C till +50 °C |
