








## Vippbrytare British Standard (BS EN 60669-1) 3-delad med vippknappar Frånkopplare



Specifikation	Artikelnr.	FE	PS	EAN
 cremevit blank	2830 01	10	29	4010337830016
 kritvit blank	2830 03	10	29	4010337830030
 antracit	2830 28	10	29	4010337830283
 alufärg	2830 26	10	29	4010337830269
 svart matt	2830 005	10	29	4010337038580
 grå matt	2830 015	10	29	4010337087113
 rostfritt stål (lackerat)	2830 600	10	29	4010337022022

### Tekniska data

Inbyggnadsdjup:	25 mm
Anslutningsarea - för ledare till:	2,5 mm <sup>2</sup>
Nominell effekt:	100 W LED-last (IEC 60669)