








Vippbrytare British Standard (BS EN 60669-1) 3-delad med vippknappar Universal-av-trapp



Specifikation	Artikelnr.	FE	PS	EAN
 cremevit blank	2832 01	10	29	4010337832010
 kritvit blank	2832 03 1850000	10	29	4010337832034
 antracit	2832 28 1850002	10	29	4010337832287
 alufärg	2832 26 1850001	10	29	4010337832263
 svart matt	2832 005	10	11	4010337038528
 grå matt	2832 015 1850414	10	11	4010337087120
 rostfritt stål (lackerat)	2832 600	10	29	4010337022053

Egenskaper

- Med skruvklämmor.

Tekniska data

Inbyggnadsdjup:	25 mm
Anslutningsarea - för ledare till:	2,5 mm ²
Nominell effekt:	100 W LED-last (IEC 60669)

Hänvisningar

- Endast för skruvfastsättning.
