








Vipprötryckknapp 3-knappars 10 A 250 V~med vippor Slutande kontakt 1-polig



Specifikation	Artikelnr.	FE	PS	EAN
 cremevit blank	2844 01	10	29	4010337082033
 kritvit blank	2844 03 1850005	10	29	4010337082040
 antracit	2844 28 1850007	10	29	4010337082064
 alufärg	2844 26 1850006	10	29	4010337082057
 svart matt	2844 005	10	29	4010337037903
 grå matt	2844 015	10	29	4010337087182
 rostfritt stål (lackerat)	2844 600	10	29	4010337021957

Egenskaper

- Med skruvklämmor.

Tekniska data

Inbyggnadsdjup: 25 mm

Anslutningsarea
- för ledare till: 2,5 mm²

Hänvisningar

- Endast för skruvfastsättning.
