








## Knappbrytare 10 AX 250 V~med rakt stående vippa 2-knappars Kronbrytare



| Specifikation   | Artikelnr.          | FE  | PS | EAN           |
|---|---------------------|-----|----|---------------|
|  kritvit blank      | 2860 201<br>1850216 | 1/5 | 01 | 4010337065876 |
|  kritvit sidenmatt | 2860 27             | 1/5 | 01 | 4010337029373 |
|  antracit          | 2860 28             | 1/5 | 11 | 4010337029397 |
|  alufärg           | 2860 26             | 1/5 | 11 | 4010337029380 |
|  svart matt        | 2860 005            | 1/5 | 11 | 4010337038023 |
|  grå matt          | 2860 015<br>1850415 | 1/5 | 11 | 4010337087199 |
|  rostfritt stål    | 2860 600            | 1/5 | 11 | 4010337021223 |

### Tekniska data

#### Inbyggnadsdjup

|            |       |
|------------|-------|
| - 2860 ... | 28 mm |
| - 2861 ... | 32 mm |

#### Anslutningsarea

|   |                     |
|---|---------------------|
| - För styva och flexibla ledare upp till: | 2,5 mm <sup>2</sup> |
|---|---------------------|

#### Nominell effekt

|               |       |
|---------------|-------|
| - LEDi/ CFLi: | 100 W |
|---------------|-------|

Bilder är liknande och kan avvika från originalet.

---

## Hänvisningar

- Beroende på tillgänglighet.

---