








## Knappbrytare 10 AX 250 V~med rakt stående vippa 2-knappars Kronbrytare



Specifikation	Artikelnr.	FE	PS	EAN
 kritvit blank	2860 201 1850216	1/5	01	4010337065876
 kritvit sidenmatt	2860 27	1/5	01	4010337029373
 antracit	2860 28	1/5	11	4010337029397
 alufärg	2860 26	1/5	11	4010337029380
 svart matt	2860 005	1/5	11	4010337038023
 grå matt	2860 015 1850415	1/5	11	4010337087199
 rostfritt stål	2860 600	1/5	11	4010337021223

### Tekniska data

#### Inbyggnadsdjup

- 2860 ...	28 mm
- 2861 ...	32 mm

#### Anslutningsarea

- För styva och flexibla ledare upp till:	2,5 mm <sup>2</sup>
---	---------------------

#### Nominell effekt

- LEDi/ CFLi:	100 W
---------------	-------

Bilder är liknande och kan avvika från originalet.

---

## Hänvisningar

- Beroende på tillgänglighet.

---